

## QUALITY CONTROL **SITU** SYSTEM

### FOR **BRAKE DISC** LASER **COATING PROCESS**



#### **SOLUTION FOR BRAKE DISC HS-LMD\* PROCESS**

DISCOVER IR SUITE is compatible with OPC-UA and integrable on PROFINET networks.











strategies

Enhanced productivity and decreased CO<sub>2</sub> emissions



DISCOVER IR SUITE provides, in-process, quality assessment (Ok, NOk)\*\* of a brake disc coating process.

A specially designed system captures, analyses and delivers key information from the process in-line.

Mathematical treatment of the extracted information allows for the identification and classification of the most common process deviations and instabilities in real-time.



#### **ADVANCED SOFTWARE**

Powerful Al-based analysis tool that detects and classifies the most common anomalies.



- Infrared imaging captured by sensor.
- Automatic background and NUC with buffered frames.
- Frame rate 1000 fps.
- Logging capabilities.
- Image segmentation.
- Image features at 1000 Hz: Visualization on a 2D disk map.
- Final score for classification (average distance).



Product image and software interface could be modified in the final product. \* High Speed Laser Metal Deposition. \*\* DISCOVER IR SUITE provides realtime process deviations and instabilities based on the reference setup by the manufacturer.


# MAIN BENEFITS ADVANTAGE OF USING DISCOVER IR SUITE

A unique system that ensures quality assurance in HS-LMD brake disc coatings.



Real-time classification of process deviations and instabilities:

- Identification of dirty and defective surfaces.
- Powder flow rate.
- Bent powder line.
- Blocked injectors.
- Variations in linear speed (feed rate).
- Nozzle misalignment.
- Powder mass flow rate.
- Tungsten Carbide content.
- Powder leaks, with the ability to quantify leak size.



#### **MAIN SPECIFICATIONS**

( (

| COMPONENTS              | Sensor head with embedded real-time processing electronics and connectors. Imaging lens. Software for system configuration and analysis. Infrared emitter for initial focus and optical calibration. |
|-------------------------|--|
| PROCESS COMPATIBILITY   | High speed LMD (Laser Metal Deposition) process.   |
| OPTICS REQUIREMENTS     | Optical path transparent to infrared radiation (above 1.1 µm) from the process area to the optical port is required.*  |
| DIMENSIONS / WEIGHT     | 84 mm x 60 mm x 42.5 mm / 0.5 kg (without connection box)  |
| POWER SUPPLY            | 24 VDC, 6W   |
| IMAGING LENS            | According to client's specifications and needs. Several optical configurations available - Manual focus.   |
| MECHANICAL ENCLOSURE    | IP65 housing with embedded waterblock for air/watercooling temperature estabilization.   |
| MECHANICAL INTERFACE    | Multiple Adapters  |
| INFRARED CAMERA         | VPD PbSe camera, 64x64 pixels (pixel size: 50 μm)<br>Sensitive in the MWIR (1-5 μm)<br>Fully Digital and snapshot type ROIC.   |
| COMMUNICATION INTERFACE | Gigabit Ethernet (Shielded M12 Connector to RJ-45)   |
| SOFTWARE                | Includes both analysis software and production software.   |
| MINIMUM REQUIREMENTS    | PC with processor i5, RAM memory: 8 GB<br>Hard disk available: 1 GB, O.S.: Windows 10 or later (32/64 bits).   |
| OTHER FEATURES          | 2x digital input, 2x digital output (multiple functionalities). Process data logging.  |

Equipment described herein is subject to Spanish export regulations and may require a license prior to export. Diversion contrary to Spanish law is prohibited. Imagery for illustration purposes only. Specifications are subject to change without notice. ©2024 New Infrared Technologies

<sup>\*</sup>The performance of the system may be limited if additional optical components are installed in the optical path.

